



THURLBY THANDAR

TF930/960 USB Virtual COM Port Drivers

This download contains the files necessary to create a virtual COM port driver on Windows operating systems from Windows 7* through to Windows 10 in both 32 and 64 bit versions. The driver is most easily installed using the plug and play capabilities of the PC operating system.

*Note: Windows 7 requires updates KB4474419 and KB4490628 installed to support the digital signature of the driver files.

Unzip the downloaded driver file to a temporary location on the PC.

Connect the TF930/960 to the PC via a USB cable; the TF930/960 will power up (if not already on) and the PC should report new hardware found.

Follow the on screen directions on the PC for loading the drivers from the folder containing the unzipped files.

Once the drivers are loaded on the PC a virtual COM port will be established each time the TF930/960 is powered up and connected to the PC. The virtual COM port will disappear if either of these conditions ceases to be true.

Note that the virtual COM port will need to be accessed at the Baud rate specified for the TF930/960 (115200 Baud). The virtual COM port is treated as a standard hardware COM port by Windows based software.

The COM port drivers will not function with earlier operating systems.

Thurlby Thandar Instruments Ltd
Glebe Road, Huntingdon, Cambs PE29 7DR
England, U.K.

Tel: 01480 412451 Fax: 01480 450409 e mail:
sales@tti-test.com web: www.tti-test.com